



[Home](#)

[Products](#)

[Support](#)

[Products](#) / [Filters, Collecto...](#) / [Replacement Filte...](#) / [Liquid Filter Ele...](#) / [Fulflo Honeycomb ...](#) / [M19R20A](#)

[Services](#)

[Solutions](#)

[Where to Buy](#)

Fulflo Honeycomb Wound Filter Cartridges | Multi-purpose design with nominal 90% efficiency from 0.5-150 micron

Part #: M19R20A



Parker has been a leader in filter media innovation and performance since we first invented the Honeycomb™ Filter Tube over 65 years ago. Parker has the world's largest manufacturing capacity for wound filter cartridges, offering superior quality.

[View Series Page](#)

[View Catalog\(s\)](#)

[Share / Email](#)

[Print](#)

Technical Specifications

Micron Rating (µm):	10	Flow Rate:	5 GPM per 10 inch
Industry:	Food and beverage	End Cap Material:	No end cap
End Cap Finish:	No end treatment	Filter Construction:	Polypropylene FDA grade
Core Cover Material:	No core cover	Core Type:	Polypropylene
Brand:	domnick hunter	Packaging:	STANDARD PACKAGING
Function:	Clarification/Prefiltration/Polishing	End Cap Configuration:	DOE
Media:	Polypropylene FDA grade	Seal Material:	No gasket
Filter Construction:	Wound	Length (inch):	20
Inside Diameter:	1 inch	Outside Diameter (inch):	2 7/16
Specifications Met:	FDA		

[Safety Warning](#)

Item Information

Parker has been a leader in filter media innovation and performance since we first invented the Honeycomb™ Filter Tube over 65 years ago. Parker has the world's largest manufacturing capacity for wound filter cartridges, offering superior quality along with technical, engineering and marketing support. Effective removal ratings at nominal 90% efficiency from 0.5µm to 150µm.

- Features/Benefits
- A broad range of media provide excellent compatibility with a variety of organic solvents, animal, petroleum and vegetable oils
 - Optional core covers and end treatments assure fiber migration control
 - Multiple length filter cartridges minimize change-out time, eliminate spacers and are available to fit competitive filter vessels
 - FDA grade polypropylene (DOE only) filter cartridges certified to ANSI/ NSF61 standard for contact with drinking water components

- Continuous and winding geometry provides performance consistency
 - Parker extended center core option eliminates the need for cartridge guides in all competitive and Fulflo® multi-cartridge vessels
 - Top center cap extender is available for polypropylene cores
 - Cotton, polypropylene, nylon and polyester materials are FDA listed as acceptable for potable and edible liquid contact according to CFR Title 21
 - O-ring/end cap options available
 - ISO9001:2008 registered company
- Home**
- Products**
- Applications
 - Oxidizing Agent Filtration
- Support**
- Petroleum Oil Filtration
 - Concentrated Filtration
- Industries**
- Solutions Filtration
 - Potable Liquid Filtration
- Services**
- Filtration
 - Dilute Acids & Alkali Filtration
- Solutions**
- Filtration
 - Prefilter for Membranes
- Where to Buy**
- Mineral Acid Filtration
 - Organic Acids & Solvent Filtration

CAD Drawings + Files



Related Documents



Parker Sales Company UK

psc.uk.webform@support.parker.com
[+44 \(0\)1926 317878](tel:+44201926317878)

+ Company Information

+ Global Operations

+ Help & Support

+ Follow Us :

© PARKER HANNIFIN CORP 2023

ENGINEERING YOUR SUCCESS.

[SITE MAP](#) [SAFETY](#) [PRIVACY POLICIES](#) [TERMS AND CONDITIONS](#)



[Home](#)

[Products](#)

[Support](#)

[Industries](#)

[Services](#)

[Solutions](#)

[Where to Buy](#)
